
	1	2	3	4		5	6
A					ITEM NO.	PRODUCT CODE	
					1	NE-AG-5060	Enclosure 530x does not norm you require drill
					2	SP-SK-PE-1.3-G	Replacement S accessories. Fo pump parts see
В					3	SP-PCB-DIGI-ORP-XP2-M	DIGICHEM-ORP Motherboard c to which circuit include process enclosure)
			PROSE		4	SP-PCB-DIGI-ORP-XP2-P-L	DIGICHEM-ORF fitted to enclos and screw dow
6					4A	SP-PCB-DIGI-ORP-XP2-P	DIGICHEM-ORP board only, to I
				STATES S	5	MAN DIGI-RX2A-P	Digi-ORP Manif Switch, 1/2" por optional Groun optional TDS Pro 2 ports for option drawing of indi RX2A-P Spares
D				6	6	SP-DCON-PB10AT-PL-0.75m	TDS probe lead
E						DIGI-AB2RX	COMPATIBL (2A-P
						CWC Conve Wo Con	ergent Di ter trols
F						DATE Details ISSU	IED BY APPROVED BY LF LF COPYRI Illimeters unless otherwise COPYRI
	1	2	3	4		FILE: C:\CWC\Library\Manufactured Proc	written

7	8		
		л А	
DESCRIPTION			`
x630x255mm Grey lid H nally come pre drilled, r rilled for a Digi-ORP syste	olease specify it		
SEKO PE-1.3 pump, sup For more detailed draw ee SEKO PE-1.3-FP-T Spa	ring of individual		
RP-XP2 Controller Replay only. (Does not include uit board is normally mo essor PCB which is fitted	e enclosure base ounted. Does not	E	3
RP-XP2 Replacement Pro osure lid, ready to plug i own onto enclosure bas	nto motherboard		
RP-XP2 Spare Processor			_
nifold. Inlet to Outlet: Bo ort for optional ORP pro und probe, sample poin Probe, includes Bleed vo tional injection valves.	bbe, 3/4" Port for It, 3/4" Port for alve, check valve, For more detailed		-
dividual manifold parts : s Drawing	see man digi-		
nd to suit TDS Probe SP-E T-P, 0.75m long (Include			)
BLE MODELS			
DIGI-AB2RX2/	A-P-CABG		
DIGI-AB2RX2A-P-	CABG	Revision ]	
ving type: oare Parts		SHEET SIZ	E
	S14	A3	
IGI-AB2RX2A-P-CABG_A yright	NO/VI	SHEET	1
e designs, concepts & specifications within this dra ater Controls Pty Ltd. They must not be copied or re tten consent from Convergent Water Controls Pty	produced wholly or in part without	SCALE	_
GI-AB2RX2A-P		1:5	
SS: 15677.64 grams			- 1

1		2	3	4		5	6	7 8	
			$\overline{7}$						
		6				ITEM NO.	PRODUCT CODE	DESCRIPTION	
						1	SP-M-BV-20-TU	True Union Ball Valve, 20mm solvent weld (Grey PVC body, red handle)	
	9					1A	SANKING SL-0242007	Replacement 3/4" EPDM O-ring for Union En	d
						2	SP-CV-INT-3/4	Internal Check valve cartridge	
5					$\bigcirc$	3	SANKING SL-242007	Barrel Union 20mm	
					(2)	4	EMEC 031.0454.0	PMMA Flow Switch Block	
						5	EMEC 108.1615.1	Flow switch float (includes 2m 2-core lead)	
	Ţ				9	6	WA OPF10-PBN10- 1.5m	General purpose platinum ORP Sensor, singl junction, 1/2" MNPT, 1.5 metre cable BNC. Supplied loose in wetted cap	e
						7	SP-DCON-CMR	Ground probe for ORP/pH System - 3/4" BSP process connection	
					10	8	SP-DCON-PB10AT-P	Conductivity Probe, Carbon Electrodes & IP68 Connector. No Lead	
						9	SP-SOL-1/2-S	Solenoid valve 1/2" 2.7 Bar Max Operating Pressure	
4						9A	SP-SOL-1/2-B	Pro-Matic solenoid valve 1/2" 10 Bar Max Operating Pressure	
						10	SP-SK-03A	0.1 bar injection valve	
				TFT		11	EMEC 028.0222.0	Ball valve 1/2" M/M Grey, including hose fitting kit 4x6 with rubber gasket fitted to one end	è
(3)	- FAI				1A	11A	EMEC 026.0306.0	Gasket EPDM to seal 1/2" hose fitting kit to EMEC ball valve 1/2" M/M grey	
						11B	EMEC 025.0217.1	Hose fitting kit (1/2" F thread, for 4x6 tube) Black PP FP	
2							MAN DIGI-RX2A-P	Manifold for DIGI-AB2RX2A-P. Includes flow switch, ground probe, solenoid valve, PVC check valve and injection valves. Does not include TDS or ORP probes, pipe clips or PVC backboard	
$\frown$								MPATIBLE MODELS	
							DIGI-AB2RX2A-P	DIGI-AB2RX2A-P-CABG	
							Converse	PRODUCT:	F
						CINC	Converger		
(1A)						CWC	Water	DRAWING TYPE:	S
						$\leq$	Controls		
						DATE 18/06/2020 Rele	Details ISSUED BY APPROVE ase Information LF LF	DRAWING NO: D BY MAN DIGI-RX2A-P_ASM	
							iensions. Dimensions are in Millimeters unless otherv ale, If in doubt consult with Convergent Water Cor	ntrols Water Controls Pty Ltd. They must not be copied or reproduced wholly or in part without	it –
						FILE: C:\CWC\Libr	ary\Manufactured Products\Manifolds\/	written consent from Convergent Water Controls Pty Ltd. MAN-DIGI-RX2A-P	
 1		2	3	1		MATERIAL: Misc		MASS: 2263.50 grams	



7	8	
DESCRIPTION		A
EKO peristaltic pumps		
ck chassis and 2 brown	rollers. Roller	
gon A-60-G 3x7.4 mm w -1.3 or PE-0.4 peristaltic p	ith grey oumps that have	
plate, new bearing an model pumps. Also inc p is the old type PE-1.3 c PE-0.4)	d 2 screws, cludes old type or PE-0.4. (Note:	В
xle Pump		
Black (2 metre roll, 6mm	n OD/4mm ID)	
to suit 4x6 tubing		
d as either one-piece w filter with ceramic weig	reighted PVDF ght that slides	
ear (2 metre roll, 6mm O	D/4mm ID)	С

BL	e models		
	SEKO PE-0.4-FP-PLUG		
	SEKO PE-1.3-FP-T-PLUG		
DUC	2]:	Revisio	on

D

SEKO PE-1.3-FP-T	]
wing type: pare Parts	SHEET SIZE
WING NO: EKO PE-1.3-FP-T_ASM	SHEET
YRIGHT e designs, concepts & specifications within this drawing are the property of Convergent ater Controls Pty Ltd. They must not be copied or reproduced wholly or in part without itten consent from Convergent Water Controls Pty Ltd.	1 OF 1
pares Drawing SS: 327.68 grams	SCALE
-	

1	1 2	3	4		5	6	7	8
				NO.	PRODUCT CODE		DESCRIPTIC	N
				1	NE-AG-5060	Enclosure s does not n you require	530x630x255mm Grey ormally come pre dri e drilled for a Digi-ORF	lid Hinged. Note: led, please specify it ? system
				2	SP-SK-PE-1.3-G	Replacem accessorie pump part	ent SEKO PE-1.3 pump s. For more detailed s see SEKO PE-1.3-FP-	o, supplied without any drawing of individual [ Spares Drawing
				3	SP-PCB-DIGI-ORP-XP2-M	Motherboo to which c	ocessor PCB which is f	clude enclosure base v mounted. Does not
				4	SP-PCB-DIGI-ORP-XP2-P-L	DIGICHEM fitted to er and screw	-ORP-XP2 Replacemenclosure lid, ready to p down onto enclosure	nt Processor Board, plug into motherboard base
				4A	SP-PCB-DIGI-ORP-XP2-P	DIGICHEM board only	-ORP-XP2 Spare Proce	essor Board (Processor xisting enclosure lid)
			5	5	MAN DIGI-RX2A-P	Digi-ORP M Switch, 1/2 optional G optional TE 2 ports for drawing of RX2A-P Spo	Manifold. Inlet to Outle "port for optional OR round probe, sample DS Probe, includes Ble optional injection value findividual manifold p ares Drawing	et: Ball valve, Flow P probe, 3/4" Port for point, 3/4" Port for ed valve, check valve ves. For more detailed parts see MAN DIGI-
			6	6	SP-DCON-PB10AT-PL-0.75n	TDS probe DCON-PB1 fitted to lea	0AT-P, 0.75m long (In	SP-DCON-PB10AT-P o cludes IP68 connector
						COMP	ATIBLE MODELS	
					DIGI-AB2R			RX2A-P-CABG
					CWC W	ergent ater ntrols	PRODUCT: DIGI-AB2RX2A DRAWING TYPE: Spare Parts - Wirefra	A-P-CABG
					DATE Details IS 19/06/2020 Release Information NOTE	ergent ater ntrols	PRODUCT: DIGI-AB2RX2A DRAWING TYPE: Spare Parts - Wirefra DRAWING NO: DIGI-AB2RX2A-P-CA COPYRIGHT	A-P-CABG me BG_ASM
					DATE Details IS 19/06/2020 Release Information	ergent ater ater ater ater btrols	PRODUCT: DIGI-AB2RX2A DRAWING TYPE: Spare Parts - Wirefra DRAWING No: DIGI-AB2RX2A-P-CA COPYRIGHT The designs, concepts & specifications with	A-P-CABG me BG_ASM hin this drawing are the property of Convergent opied or reproduced wholly or in part without

	1	2		3		4		5	6	7	8	
		(	6 (7)	8								
4			$\sim$					ITEM NO.	PRODUCT CODE	DESCRI		_
						$\mathcal{T}$		1	SP-M-BV-20-TU	True Union Ball Valve, 20 (Grey PVC body, red ho	andle)	_
					$\sum$			1A	SANKING SL-0242007	Replacement 3/4" EPDN	1 O-ring for Union Enc	ł
	(5)							2	SP-CV-INT-3/4	Internal Check valve co	ırtridge	
	$\mathbf{U}$						2	3	SANKING SL-242007	Barrel Union 20mm		
	ł				RATE .		~	4	EMEC 031.0454.0	PMMA Flow Switch Block	k	
			$\mathcal{L}$					5	EMEC 108.1615.1	Flow switch float (includ	es 2m 2-core lead)	
							9	6	WA OPF10-PBN10- 1.5m	General purpose platinu junction, 1/2" MNPT, 1.5 Supplied loose in wetted	um ORP Sensor, single metre cable BNC. d cap	;
_								7	SP-DCON-CMR	Ground probe for ORP/ process connection	oH System - 3/4" BSP	
					O D	Y CES	(10)	8	SP-DCON-PB10AT-P	Conductivity Probe, Car IP68 Connector. No Lec	rbon Electrodes & ad	
								9	SP-SOL-1/2-S	Solenoid valve 1/2" 2.7 E Pressure	3ar Max Operating	
	4							9A	SP-SOL-1/2-B	Pro-Matic solenoid valve Operating Pressure	e 1/2" 10 Bar Max	
			(11A)				1	10	SP-SK-03A	0.1 bar injection valve		
			(11A) (11B)	-				11	EMEC 028.0222.0	Ball valve 1/2" M/M Grey fitting kit 4x6 with rubber end	y, including hose gasket fitted to one	
	3	A H					(1A)	11A	EMEC 026.0306.0	Gasket EPDM to seal 1/ EMEC ball valve 1/2" M/	2" hose fitting kit to M grey	
					6 th Car			11B	EMEC 025.0217.1	Hose fitting kit (1/2" F thr Black PP FP	ead, for 4x6 tube)	
	2								MAN DIGI-RX2A-P	Manifold for DIGI-AB2RX switch, ground probe, so check valve and injection include TDS or ORP prob backboard	olenoid valve, PVC on valves. Does not	
		H										
	Ŕ	FTM							COI	MPATIBLE MODELS		
	1								DIGI-AB2RX2A-P	DIGI-AB2	rx2a-p-cabg	
									Converger	MAN DIGI-RX2	2A-P	Rev
									Water Controls	DRAWING TYPE: Spare Parts - Wirefram	ne	SHE
	$\mathcal{A}$							DATE	Details ISSUED BY APPROVE		24.4	A
	l							18/06/2020 Rele	ase Information LF LF	MAN DIGI-RAZA-P_A	SIVI	SI
									ensions. Dimensions are in Millimeters unless otherw ale. If in doubt consult with Convergent Water Cor		n this drawing are the property of Convergen pied or reproduced wholly or in part without ntrols Pty Ltd.	
								FILE: C:\CWC\Libro	ary\Manufactured Products\Manifolds\A		· · · · · · · · · · · · · · · · · · ·	
	1	2		3		4		MATERIAL: Misc		MASS: 2263.50 grams		

	1 2	3		4		5	6	7	8
A					ITEM NO.	PRODUCT CODE		DESCRIPTION	A
					1	SP-SK-08	SEKO Wall bracket fo	or SEKO peristaltic pumps	
					2	SP-SK-06		black chassis and 2 brown roller	s. Roller
					3	SP-SK-01A-BK-TY	SP-SK-06 rotor assem		
В		(2)			4	SP-SK-07-T-A-KIT	Kit containing new for suitable for 2015 or lo face plate in case p Screws not required	ace plate, new bearing and 2 so ater model pumps. Also include: ump is the old type PE-1.3 or PE- for PE-0.4)	crews, s old type 0.4. (Note: B
			3		4A	SP-SK-10	Bearing for SEKO Tra		
		$\overline{\nabla}$	$\bigcup$	(4A)	5	SP-SK-02B-BK	SEKO Discharge tubi	ng Black (2 metre roll, 6mm OD/	4mm ID)
		<u>263</u>		47	6	SP-SK-03A	Injection valve 1/2" E	3SP, to suit 4x6 tubing	
					7	SP-SK-04	SEKO Foot filter (supp assembly or as black over tube)	blied as either one-piece weight PP filter with ceramic weight th	ed PVDF at slides
С					8	SP-SK-02A	SEKO Suction tubing	Clear (2 metre roll, 6mm OD/4m	im ID) C
D					0	•			E
			(	4			COMP	ATIBLE MODELS	
F				$\bigcirc$		SE	EKO PE-0.4-FP	SEKO PE-0.4-FP-P	LUG
			(5)			SE	KO PE-1.3-FP-T	SEKO PE-1.3-FP-T-F	PLUG
	8						Convergent	SEKO PE-1.3-FP-T	Revision
		6	)				Water Controls	DRAWING TYPE: Spare Parts - Wireframe	SHEET SIZE
						DATE Deta		DRAWING NO: SEKO PE-1.3-FP-T_ASM	A3 Sheet
F						2/06/2020 Release Info		COPYRIGHT	1 OF 1
							Dimensions are in Millimeters unless otherwise doubt consult with Convergent Water Controls	The designs, concepts & specifications within this drawing are the Water Controls Pty Ltd. They must not be copied or reproduced written consent from Convergent Water Controls Pty Ltd.	e property of Convergent
	1 2	3		4		FILE: C:\CWC\Library\Pro	oducts From Suppliers\SEKO\Seko Pump		1:2
	I Z	5		7		MIGIENIAL MISC		MASS: 327.68 grams	